

Rittal – The System.

Faster – better – everywhere.



TS 9963.490

TS IT Industry 4.0 / Edge

State: 4/24/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 9963.490 - TS IT Industry 4.0 / Edge

TS IT Enclosure sealed for direct enclosure-specific climate control.

Features

Model No.	TS 9963.490
Product description	TS IT UL Type 12, 19" mounting angles, HWD: 2000 x 600 x 1000 mm, 42 U
Material	Carbon steel Front and rear door: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated Interior installation: Dipcoat-primed
General color	RAL 7035
Color	Housing frame, panels and interior fittings: RAL 7035
Supply includes	Enclosure frame Front and rear door: carbon steel, 1.5 mm Lock front and rear: Comfort handle and security lock 12321 Connection accessories for potential equalization with earthing point (supplied loose) 50 multi-tooth screws M6, captive nuts M6, conductive (supplied loose) IPPC pallet Roof plate, one-piece, solid Base, gland plate(s)
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 1,000 mm Width: 23.6 " Height: 78.7 " Depth: 39.4 "
Height units	42 U
Mounting space to 19" level, front/rear	66 mm / 189 mm

Features

Distance between mounting levels	742 mm 29.2 "
Design doors	Solid
Design of 19" mounting level(s)	Profile rails, 482.6 mm (19")
Load capacity	15,000 N
Note	The door-opening angle may vary depending on site requirements or applications
Customs tariff number	9403200082
