

Rittal – The System.

Faster – better – everywhere.



TS 9966.010

Side wall, screwable, carbon steel

State: 2/10/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

TS 9966.010 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 9966.010
Benefits	Automatic potential equalization and higher EMC protection thanks to enclosure panel holders with grounding insert Easy positioning with the location aid Grounding bolt with contact surface
Material	Carbon steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Color	RAL 9005
Supply includes	Assembly components
Note	Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure. Area available for population: External dimension – 100 mm
Suitable for	Enclosure type: TS TS IT Height: = 1,200 mm Depth: = 800 mm Enclosure type: TS TS IT Height: = 47.2 “ Depth: = 31.5 “
Protection category IP to IEC 60 529	IP 55
Base material	Carbon steel
Packaging unit	2 pc(s).
Customs tariff number	9403999040
UPC-Code	89575

Features

ETIM 9

EC002524

ECLASS 8.0

27182101