

Rittal – The System.

Faster – better – everywhere.



TS 9969.312

Side wall, screwable, carbon steel

State: 5/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

TS 9969.312 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.



Features

Model No.	TS 9969.312
Benefits	Automatic potential equalization and higher EMC protection thanks to enclosure panel holders with grounding insert Easy positioning with the location aid Grounding bolt with contact surface
Material	Carbon steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Color	RAL 7035
Supply includes	Assembly components
Note	Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure. Area available for population: External dimension – 100 mm
Suitable for	Enclosure type: TS TS IT Height: = 2,200 mm Depth: = 1,050 mm Enclosure type: TS TS IT Height: = 86.6 ″ Depth: = 41.3 ″

Features

Protection category IP to IEC 60529	IP 55
-------------------------------------	-------

Base material	Carbon steel
---------------	--------------

Packaging unit	2 pc(s).
----------------	----------

Customs tariff number	9403999040
-----------------------	------------

ETIM 9	EC002524
--------	----------

ECLASS 8.0	27182101
------------	----------