

Rittal – The System.

Faster – better – everywhere.



TS 9969.582

3-part EL NEMA 12 enclosure

State: 6/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 9969.582 - 3-part EL NEMA 12 enclosure with punched rails

The Rittal NEMA 12 3-Part EL wallmount enclosure is ideal for small networks or floor distribution in environments that require a high degree of security and a high industrial protection rating.

Features

| | |
|---------------------|--|
| Model No. | TS 9969.582 |
| Product description | All standard models feature usable panel heights from 12U to 21U and ensure safe packaging for sensitive components as well as protection from the environment and from unauthorized access. |
| Material | Wall and hinged part: carbon steel, 16 ga (15 mm) Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Color | Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray) |
| Supply includes | Wall section Hinged part with 25 mm hole pattern of holes in the front and rear frame Designer viewing door Security lock 3524 E Comfort handle and 2-point lock for 18-21 U Wall section: Flange (gland) plate, solid, top and bottom Wall section: 2 vertical punched rails Horizontal C rail for cable clamping Hinged part: 19" (482.6 mm) profile rails, fully dept adjustable Wall mounting bracket, 10 mm (0.39 in.) |
| Clearances | Clearance width: 502 mm Clearance height: 949 mm Clearance width: 19.8 ~ Clearance height: 37.4 ~ |
| Clearance height | 949 mm 37.4 ~ |

Features

| | |
|--|--|
| Depth hinged part | 445 mm 17.5 " |
| Depth of wall section | 135 mm 5.31 " |
| Clearance width | 502 mm 19.8 " |
| Load capacity of hinged part (static) | 75 kg 165.3 lb. |
| Dimensions | Width: 600 mm Height: 1,016 mm Depth: 600 mm Width: 23.6 " Height: 40 " Depth: 23.6 " |
| Packaging unit | 1 pc(s). |
| Net weight | 122.798 lb |
| Gross weight | 122.798 lb |
| Customs tariff number | 9403999040 |
