Rittal – The System.

Faster – better – everywhere.



# WM 9975.001

# Deep Hinged Window Kits

State: 11/4/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# WM 9975.001 - Deep Hinged Window Kits Carbon steel

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required.  Material carbon steel.

## Features

| | |
|---|---|
| Model No. | WM 9975.001 |
| Product description | The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal’s standard wall-mount, free-standing TS8/SE8 and other enclosure panels. Window depth allows for use of extra deep pushbuttons (~2”/50mm). It comes with a full-size drill template for easy mounting. |
| Material | Frame: Carbon steel |
| Surface finish | Dipcoat-primed and powder-coated, textured paint |
| Color | RAL 7035 |
| Supply includes | Oil resistant gasket<br>Fasteners |
| Visible area | Viewing window width: 125 mm<br>Viewing window height: 300 mm<br>Viewing window width: 4.92 ″<br>Viewing window height: 11.8 ″ |
| Viewing window height | 300 mm<br>11.8 ″ |
| Dimensions | Width: 300 mm<br>Height: 400 mm<br>Depth: 70 mm<br>Width: 11.8 ″<br>Height: 15.7 ″<br>Depth: 2.76 ″ |
| Packaging unit | 1 pc(s). |
| Net weight | 10.692 lb |

© Rittal 2026

# Features

| | |
|---|---|
| Gross weight | 10.692 lb |
| Customs tariff number | 9403999040 |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |