

Rittal – The System.

Faster – better – everywhere.



WM 9975.004 Deep Hinged Window Kits

State: 4/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 9975.004 - Deep Hinged Window Kits Carbon steel

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. Material carbon steel.

Features

Model No.	WM 9975.004
Product description	The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal's standard wall-mount, free-standing TS8/SE8 and other enclosure panels. Window depth allows for use of extra deep pushbuttons (~2"/50mm). It comes with a full-size drill template for easy mounting.
Material	Frame: Carbon steel
Surface finish	Dipcoat-primed and powder-coated, textured paint
Color	RAL 7035
Supply includes	Oil resistant gasket Fasteners
Visible area	Viewing window width: 325 mm Viewing window height: 500 mm Viewing window width: 12.8 " Viewing window height: 19.7 "
Viewing window height	500 mm 19.7 "
Dimensions	Width: 500 mm Height: 600 mm Depth: 70 mm Width: 19.7 " Height: 23.6 " Depth: 2.76 "
Packaging unit	1 pc(s).
Net weight	20.304 lb

Features

Gross weight	20.304 lb
--------------	-----------

Customs tariff number	9403999040
-----------------------	------------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------