Rittal – The System.

Faster – better – everywhere.



WM 9975.005
Deep Hinged Window Kits

State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

WM 9975.005 - Deep Hinged Window Kits Carbon steel

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. Material carbon steel.

Features

Model No.	WM 9975.005
Product description	The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal’s standard wall-mount, free-standing TS8/SE8 and other enclosure panels. Window depth allows for use of extra deep pushbuttons (~2”/50mm). It comes with a full-size drill template for easy mounting.
Material	Frame: Carbon steel
Surface finish	Dipcoat-primed and powder-coated, textured paint
Color	RAL 7035
Supply includes	Oil resistant gasket Fasteners
Visible area	Viewing window width: 415 mm Viewing window height: 660 mm Viewing window width: 16.3 ″ Viewing window height: 26 ″
Viewing window height	660 mm 26 ″
Dimensions	Width: 600 mm Height: 760 mm Depth: 70 mm Width: 23.6 ″ Height: 29.9 ″ Depth: 2.76 ″
Packaging unit	1 pc(s).
Net weight	27.756 lb

© Rittal 2026

Features

Gross weight	27.756 lb
Customs tariff number	9403999040

Approvals

Approvals	UL + C-UL (listed)