


Rittal – The System.

Faster – better – everywhere.



WM 9975.013

Deep Hinged Window Kits

State: 10/2/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 9975.013 - Deep Hinged Window Kits Stainless steel

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. Material stainless steel 1.4301 (AISI 304) or stainless steel 1.4404 (AISI 316L).

Features

Model No.	WM 9975.013
Product description	The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal's standard wall-mount, free-standing TS8/SE8 and other enclosure panels. Window depth allows for use of extra deep pushbuttons (~2"/50mm). It comes with a full-size drill template for easy mounting.
Material	Viewing window: Polycarbonate Frame: Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed
Supply includes	Oil resistant gasket Fasteners
Visible area	Viewing window width: 415 mm Viewing window height: 780 mm Viewing window width: 16.3 " Viewing window height: 30.7 "
Viewing window height	780 mm 30.7 "
Dimensions	Width: 600 mm Height: 900 mm Depth: 70 mm Width: 23.6 " Height: 35.4 " Depth: 2.76 "
Packaging unit	1 pc(s).

Features

Net weight	30.159
Gross weight	30.159
Customs tariff number	9403999040
UPC-Code	87533

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------