Rittal – The System.

Faster – better – everywhere.



WM 9975.016
Deep Hinged Window Kits

State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

WM 9975.016 - Deep Hinged Window Kits Stainless steel

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. Material stainless steel 1.4301 (AISI 304) or stainless steel 1.4404 (AISI 316L).

Features

Model No.	WM 9975.016
Product description	The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal's standard wall-mount, free-standing TS8/SE8 and other enclosure panels. Window depth allows for use of extra deep pushbuttons (~2"/50mm). It comes with a full-size drill template for easy mounting.
Material	Viewing window: Polycarbonate Frame: Stainless steel 1.4404 (AISI 316L)
Surface finish	Brushed
Supply includes	Oil resistant gasket Fasteners
Visible area	Viewing window width: 225 mm Viewing window height: 400 mm Viewing window width: 8.86 ″ Viewing window height: 15.7 ″
Viewing window height	400 mm 15.7 ″
Dimensions	Width: 400 mm Height: 500 mm Depth: 70 mm Width: 15.7 ″ Height: 19.7 ″ Depth: 2.76 ″
Packaging unit	1 pc(s).

© Rittal 2026

Features

Net weight	15.608 lb
Gross weight	15.608 lb
Customs tariff number	9403999040

Approvals

Approvals	UL + C-UL (listed)