

Rittal – The System.

Faster – better – everywhere.



WM 9975.053 Deep Hinged Window Kits

State: 6/20/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 9975.053 - Deep Hinged Window Kits Carbon steel

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. Material carbon steel.

Features

| | |
|-----------------------|---|
| Model No. | WM 9975.053 |
| Product description | The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal's standard wall-mount, free-standing TS8/SE8 and other enclosure panels. Window depth allows for use of extra deep pushbuttons (~2"/50mm). It comes with a full-size drill template for easy mounting. |
| Material | Frame: Carbon steel |
| Surface finish | Dipcoat-primed and powder-coated, textured paint |
| Color | RAL 7035 |
| Supply includes | Oil resistant gasket Fasteners |
| Visible area | Viewing window width: 275 mm Viewing window height: 250 mm Viewing window width: 10.8 " Viewing window height: 9.84 " |
| Viewing window height | 250 mm 9.84 " |
| Dimensions | Width: 450 mm Height: 350 mm Depth: 70 mm Width: 17.7 " Height: 13.8 " Depth: 2.76 " |
| Packaging unit | 1 pc(s). |
| Gross weight | 13.999 lb |

Features

Customs tariff number 9403999040

Approvals

Approvals UL + C-UL (listed)