

# Rittal – The System.

Faster – better – everywhere.



## WM 9975.056 Deep Hinged Window Kits

State: 6/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 9975.056 - Deep Hinged Window Kits Stainless steel

The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. Material stainless steel 1.4301 (AISI 304) or stainless steel 1.4404 (AISI 316L).

## Features

Model No.	WM 9975.056
Product description	The Deep-Hinged Window Kit (WKDH) is used as a viewing window where access to components mounted behind the window is required. It is designed to protect HMI displays and components mounted on enclosure panels from wash-down, rain, snow, sleet, dirt and dust. WKDH fits on the usable area of Rittal's standard wall-mount, free-standing TS8/SE8 and other enclosure panels. Window depth allows for use of extra deep pushbuttons (~2"/50mm). It comes with a full-size drill template for easy mounting.
Material	Viewing window: Polycarbonate Frame: Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed
Supply includes	Oil resistant gasket Fasteners
Visible area	Viewing window width: 275 mm Viewing window height: 250 mm Viewing window width: 10.8 " Viewing window height: 9.84 "
Viewing window height	250 mm 9.84 "
Dimensions	Width: 450 mm Height: 350 mm Depth: 70 mm Width: 17.7 " Height: 13.8 " Depth: 2.76 "
Packaging unit	1 pc(s).

## Features

---

Gross weight	13.999 lb
Customs tariff number	9403999040

---

## Approvals

---

Approvals	UL + C-UL (listed)
-----------	--------------------