
Rittal – The System.

Faster – better – everywhere.



TS 9977.470

TS 8 freestanding enclosures

State: 11/15/2021 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 9977.470 - TS 8 freestanding enclosures Stainless steel

Baying systems TS 8 with mounting plate. Protection category IP 66 (UL Type 4X). Manufactured in stainless steel 1.4404 (AISI 316L) Enclosure widths include 600 and 800 mm.







Features

Model No.	TS 9977.470
Material	Enclosure frame: Stainless steel 1.4404 (AISI 316L), 1.5 mm Roof: Stainless steel 1.4404 (AISI 316L), 1.5 mm, exterior brushed Door: Stainless steel 1.4404 (AISI 316L), 2.0 mm, exterior brushed Rear panel: Stainless steel 1.4404 (AISI 316L), 1.5 mm, exterior brushed Gland plate: Stainless steel 1.4404 (AISI 316L), 2.5 mm
Surface finish	Enclosure frame and base plates: Uncoated Door, roof and rear panel: Exterior brushed, grain size 400 Mounting panel: Zinc-plated
Supply includes	Gland plate Padlockable handle

© Rittal 2026

Features

Dimensions	Width: 600 mm Height: 2,000 mm Depth: 600 mm Width: 23.6 ″ Height: 78.7 ″ Depth: 23.6 ″
Packaging unit	1 pc(s).
Gross weight	300 lb
Customs tariff number	9403200082

Approvals

Approvals	UL + C-UL (listed)