## Rittal – The System.

Faster – better – everywhere.





POWER DISTRIBUTION > CLIMATE CONTROL





# TS 9977.475 - TS 8 freestanding enclosures Stainless steel

Baying systems TS 8 with mounting plate. Protection category IP 66 (UL Type 4X). Manufactured in stainless steel 1.4404 (AISI 316L) Enclosure widths include 600 and 800 mm.







2

#### **Features**

Model No.	TS 9977.475
	10 9977.470
Material	Enclosure frame: Stainless steel 1.4404 (AISI 316L), 1.5 mm
	Roof: Stainless steel 1.4404 (AISI 316L), 1.5 mm, exterior brushed
	Door: Stainless steel 1.4404 (AISI 316L), 2.0 mm, exterior brushed
	Rear panel: Stainless steel 1.4404 (AISI 316L), 1.5 mm, exterior
	brushed
	Gland plate: Stainless steel 1.4404 (AISI 316L), 2.5 mm
Surface finish	Enclosure frame and base plates: Uncoated
	Door, roof and rear panel: Exterior brushed, grain size 400
	Mounting panel: Zinc-plated
Supply includes	Gland plate
	Padlockable handle

© Rittal 2025

### Features

Dimensions	Width: 800 mm
	Height: 1,800 mm
	Depth: 600 mm
	Width: 31.5 "
	Height: 70.9 "
	Depth: 23.6 "
Packaging unit	1 pc(s).
Gross weight	573
Customs tariff number	9403999040
UPC-Code	88046

## **Approvals**

Approvals UL + C-UL (listed)

© Rittal 2025 3