

Rittal – The System.

Faster – better – everywhere.



undefined 9980.094

NEMA 3R Vented Outdoor Enclosure

State: 4/20/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 9980.094 - NEMA 3R Vented Outdoor Enclosure

The Wall-Mounted NEMA 3R Vented Outdoor Enclosure is a single door enclosure with roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.



Features

| | |
|---------------------|---|
| Model No. | 9980.094 |
| Product description | The NEMA 3R Vented Outdoor Enclosure is a single door enclosure with a roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters. |
| Material | Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010) |
| General color | RAL 9003 |
| Color | White |
| Supply includes | Housing with vented roof module Door with fitted seal and vented hood Mounting panel Top-mounted 115V fans Thermostat Washable Filter kits |

Features

| | |
|--------------------------------------|--|
| Dimensions | Width: 609 mm Height: 709 mm Depth: 304 mm Width: 24 " Height: 27.9 " Depth: 12 " |
| Dimensions of mounting plate (W x H) | 549 mm x 570 mm 21.6 " x 22.4 " |
| Lock | Lock version: Cam No. of locks: 2 Lock Insert: Screwdriver |
| Type rating according to UL 50E | UL Type 3R UL Type 1 UL Type 12 |
| Protection category NEMA | NEMA 3R NEMA 1 NEMA 12 |
| Material thickness - door | 2 mm 0.08 " |
| Material thickness - enclosure | 1.5 mm 0.06 " |
| Material thickness – mounting plate | 2.5 mm 0.1 " |
| Rated current | 0.23 A |
| Number of fans | 1 |
| Air throughput (unimpeded air flow) | 75 cfm |
| Fan size | 4 in |
| Packaging unit | 1 pc(s). |
| Net weight | 82.169 lb |
| Gross weight | 82.169 lb |
| Customs tariff number | 9403999040 |

Approvals

Approvals

UL + C-UL (listed)