Rittal - The System.

Faster – better – everywhere.





undefined 9980.094 NEMA 3R Vented Outdoor Enclosure

State: 11/25/2025 (Source: rittal.com/us-en)



undefined 9980.094 - NEMA 3R Vented Outdoor Enclosure

The Wall-Mounted NEMA 3R Vented Outdoor Enclosure is a single door enclosure with roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.







Features

Model No.	9980.094
Product description	The NEMA 3R Vented Outdoor Enclosure is a single door enclosure with a roof module and door hood. The configuration includes predrilled mounting holes and integrated cooling with fans and filters.
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010)
General color	RAL 9003
Color	White
Supply includes	Housing with vented roof module Door with fitted seal and vented hood Mounting panel Top-mounted 115V fans Thermostat Washable Filter kits

© Rittal 2025 2

Features

Dimensions	Width: 609 mm Height: 709 mm Depth: 304 mm Width: 24 " Height: 27.9 " Depth: 12 "
Dimensions of mounting plate (W x H)	549 mm x 570 mm 21.6 ″ x 22.4 ″
Lock	Lock version: Cam No. of locks: 2 Lock Insert: Screwdriver
Type rating according to UL 50E	UL Type 3R UL Type 1 UL Type 12
Protection category NEMA	NEMA 3R NEMA 1 NEMA 12
Material thickness - door	2 mm 0.08 "
Material thickness - enclosure	1.5 mm 0.06 ″
Material thickness – mounting plate	2.5 mm 0.1 "
Rated current	0.23 A
Number of fans	1
Air throughput (unimpeded air flow)	75 cfm
Fan Size	4 in
Weight/packaging unit	82 lb. 1,312 oz.
Packaging unit	1 pc(s).
Net weight	82.169
Customs tariff number	9403999040

© Rittal 2025 3

Features

UPC-Code 92345

Approvals

Approvals UL + C-UL (listed)

© Rittal 2025