Rittal – The System.

Faster – better – everywhere.



undefined 9980.125

NEMA 3R Vented Outdoor Enclosure

State: 11/13/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

undefined 9980.125 - NEMA 3R Vented Outdoor Enclosure

The Wall-Mounted NEMA 3R Vented Outdoor Enclosure is a single door enclosure with roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.







Features

Model No.	9980.125
Product description	The NEMA 3R Vented Outdoor Enclosure is a single door enclosure with a roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010)
General color	RAL 9003
Color	White
Supply includes	Housing with vented roof module Door with fitted seal and vented hood Mounting panel Top-mounted 115V fans Thermostat Washable Filter kits

© Rittal 2026

Features

Dimensions	Width: 909 mm Height: 1,634 mm Depth: 504 mm Width: 35.8 ″ Height: 64.3 ″ Depth: 19.8 ″
Dimensions of mounting plate (W x H)	840 mm x 1,455 mm 33.1 ″ x 57.3 ″
Lock	Lock version: Cam No. of locks: 3 Lock Insert: Screwdriver
Type rating according to 508A	UL Type 3R UL Type 1 UL Type 12
Protection category NEMA	NEMA 3R NEMA 1 NEMA 12
Material thickness - door	2 mm 0.08 ″
Material thickness - enclosure	2 mm 0.08 ″
Material thickness – mounting plate	2.5 mm 0.1 ″
Rated current	1 A
Number of fans	3
Air throughput (unimpeded air flow)	500 cfm
Fan size	6 in
Packaging unit	1 pc(s).
Customs tariff number	9403999040

Approvals

Approvals	UL + C-UL (listed)