


# Rittal – The System.

Faster – better – everywhere.



## IT 9982.124

## Network/server enclosures TS IT

State: 3/4/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 9982.124 - Network/server enclosures TS IT with vented door, pre-configured, RAL 9005, North American version

TS IT pre-configured with standard accessories. RAL 9005 (Black). Enclosures are complete with depth variable 482.6mm (19”) profile rails, casters, cable management, PDU brackets and locking front and rear vented doors. Available in a range of size variants with optional sidewalls and baying kits.

## Features

|                     |                                                                                                                                                                                                                                                                                                            |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.           | IT 9982.124                                                                                                                                                                                                                                                                                                |
| Product description | TS IT pre-configured with standard accessories. RAL 9005 (Black). Enclosures are complete with depth variable 482.6mm (19”) profile rails, casters, cable management, PDU brackets and locking front and rear vented doors. Available in a range of size variants with optional sidewalls and baying kits. |
| Material            | Carbon steel<br>Aluminum                                                                                                                                                                                                                                                                                   |
| Surface finish      | Enclosure frame: Dipcoat-primed<br>Interior installation: Dipcoat-primed<br>Doors and roof: Dipcoat-primed, powder coated                                                                                                                                                                                  |
| General color       | RAL 9005                                                                                                                                                                                                                                                                                                   |
| Color               | Enclosure frame and panels: RAL 9005<br>Interior installation: RAL 9005                                                                                                                                                                                                                                    |

# Features

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|--------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Supply includes                      | Enclosure frame TS 8 with door and roof plate<br>Aluminum carbon steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges<br>Carbon steel door at rear, ventilated in one piece (free area in perforated carbon steel part approx. 85 %), 130° hinges<br>Front and rear comfort handles with push button keyed door lock<br>Installed caster kits<br>Installed leveling feet<br>M6 cage nuts (Package of 100)<br>M6 mounting screws (Package of 100)<br>Solid sidewalls, pre-installed<br>PDU brackets (shipped loose)<br>Cable management wall, pre-installed |
| Dimensions                           | Width: 600 mm<br>Height: 2,200 mm<br>Depth: 1,050 mm<br>Width: 23.6 "<br>Height: 86.6 "<br>Depth: 41.3 "                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Installation height for components   | 47 U                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Load capacity of the 19" levels      | 10,000 N                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Note                                 | The door-opening angle may vary depending on site requirements or applications<br>with side panels                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Distance between levels as delivered | 745 mm<br>29.3 "                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Design of 19" mounting level(s)      | Profile rails, 482.6 mm (19")                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Design doors                         | Vented                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Packaging unit                       | 1 pc(s).                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Gross weight                         | 362.95 lb                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Customs tariff number                | 9403999040                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |

# Approvals

---

Approvals

UL + C-UL (listed)