Rittal – The System.

Faster – better – everywhere.



IT 9982.226

TS IT Pro racks, Shiploadable

State: 11/3/2026 (Source: www.rittal.com/us-en)

IT 9982.226 - TS IT Pro racks, Shiploadable

TS IT Pro configured for ready deployment. Enclosures are complete with depth adjustable 19" EIA rails, casters, right and left cable management walls each with dual PDU mounting, baying kit and locking front and rear perforated doors. Robust packaging system designed for safe equipment integration, transportation, and on site deployment. Meets ISTA 3E standards. Available in a range of sizes with sidewalls.

Features

Model No.	IT 9982.226
Product description	TS IT Pro configured for ready deployment. Enclosures are complete with depth adjustable 19" EIA rails, casters, right and left cable management walls each with dual PDU mounting, baying kit and locking front and rear perforated doors. Robust packaging system designed for safe equipment integration, transportation, and on site deployment. Meets ISTA 3E standards. Available in a range of sizes with sidewalls.
Material	Carbon steel
General color	RAL 9005
Color	Black RAL 9005

© Rittal 2026

Features

Supply includes	Perforated single steel door at the front (85% perforated) 145° quick release security hinges Perforated steel door at the rear vertically divided (85% perforated) 145° quick release security hinges Roof cable access with brushed baffles Front and rear comfort handles with push button keyed door lock Preinstalled heavy-duty casters Leveling feet (Package of 4 shipped loose) Fully welded steel frame 19" EIA rails printed with U markings on the front and back of each rail M6 cage nuts (Package of 50) M6 mounting screws (Package of 50) Two moveable cable management walls with dual PDU mounting and cable manager cutouts Half-height quick release locking sidewalls keyed to match door locks Engineered shock pallet for safe transportation of IT equipment Three piece rugged shell Included ramp for unloading on site
Dimensions	Width: 600 mm Height: 2,012 mm Depth: 1,070 mm Width: 23.6 ″ Height: 79.2 ″ Depth: 42.1 ″
Height units	42 U
Height units	42 U
Version	Pre-configured
Design doors	Perforated front and rear
Packaging unit	1 pc(s).
Customs tariff number	9403200082