

Rittal – The System.

Faster – better – everywhere.



TS 9982.308

TS IT Industry 4.0 / Edge

State: 6/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 9982.308 - TS IT Industry 4.0 / Edge

TS IT Enclosure sealed for direct enclosure-specific climate control.

Features

Model No.	TS 9982.308
Product description	TS IT NEMA 12, 19" mounting angles, viewing door, HWD: 2000 x 800 x 1200 mm, 42 U
Material	Carbon steel Viewing door: Polycarbonate, 3 mm
Surface finish	Enclosure frame: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated Interior installation: Dipcoat-primed
General color	RAL 7035
Color	Housing frame, panels and interior fittings: RAL 7035
Supply includes	Enclosure frame Viewing front and solid rear door Lock front and rear: Comfort handle and security lock 12321 Front and rear 482.6 mm (19") Z-rail mounting sections, depth adjustable mounting Connection accessories for potential equalization with earthing point (supplied loose) 50 multi-tooth screws M6, captive nuts M6, conductive (supplied loose) IPPC pallet Roof plate, one-piece, solid Base, gland plate(s)
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 1,200 mm Width: 31.5 " Height: 78.7 " Depth: 47.2 "
Height units	42 U

Features

Mounting space to 19" level, front/ rear	66 mm / 189 mm
Distance between mounting levels	742 mm 29.2 "
Design doors	Solid
Design of 19" mounting level(s)	Profile rails, 482.6 mm (19")
Load capacity	15,000 N
Note	The door-opening angle may vary depending on site requirements or applications
Customs tariff number	9403200082
