

Rittal – The System.

Faster – better – everywhere.

Wire end ferrules loose – AS 4050.732

Date : 19.4.2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wire end ferrules loose – AS 4050.732

created: 19.04.2021 build on www.rittal.com/si-sl



Product description

Description: With plastic collar.

Technical specifications: Heat-resistant to 105 °C

Standards: AEH DIN 46228

Material: E-Cu, galvanic tin-plated
Plastic collar: Polypropylene

Note: UL-certified in conjunction with the relevant tools, such as crimping machines.

Product description

For cross-section: 1 mm²

AWG: 18

Length: 8 mm

Internal diameter: 3 mm

Design: for wire processing machines

Colour: Red

Colour code: DIN colour code: yes

For:	Crimping machine L8 manual wire processing
Delivery form:	Loose
Packs of:	500 pc(s).
Weight/pack:	0,5 kg
Copper weight (kg per piece):	0
EAN:	4028177805002
Customs tariff number:	85369010
ETIM 7.0:	EC000005
ETIM 6.0:	EC000005
eCl@ss 8.0/8.1:	36659290
eCl@ss 6.0/6.1:	36659290
Product description:	Wire end ferrules According to DIN colour code
Approvals	
Approvals:	UL + C-UL UR