

Rittal – The System.

Faster – better – everywhere.

Wire end ferrules on a reel – AS 4050.746

Date : 4.11.2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wire end ferrules on a reel – AS 4050.746

created: 04.11.2019 build on www.rittal.com/si-sl



Product description

Description:	With plastic collar.
Technical specifications:	Heat-resistant to 105 °C
Standards:	AEH DIN 46228
Material:	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Note:	UL-certified in conjunction with the relevant tools, such as crimping machines.

Product features

For cross-section:	0,5 mm ²
AWG:	20
Length:	8 mm
Internal diameter:	2,6 mm
Design:	for wire processing machines
Colour:	White
Colour code:	DIN colour code: yes

For: Crimping machine RC
Crimping machine R8
Crimping machine R8 E

Delivery form: Taped

Packs of: 5000 pc(s).

Copper weight (kg per piece): 0

EAN: 4028177805149

Customs tariff number: 85369010

ETIM 7.0: EC000005

ETIM 6.0: EC000005

eCl@ss 8.0/8.1: 36659290

eCl@ss 6.0/6.1: 36659290

Product description: Wire end ferrules According to DIN colour code

Approvals

Approvals: UR
