

Rittal – The System.

Faster – better – everywhere.

Wire end ferrules on a reel – AS 4050.748

Date : 27.11.2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wire end ferrules on a reel – AS 4050.748

created: 27.11.2019 build on www.rittal.com/si-sl



Product description

Description: With plastic collar.

Technical specifications: Heat-resistant to 105 °C

Standards: AEH DIN 46228

Material: E-Cu, galvanic tin-plated
Plastic collar: Polypropylene

Note: UL-certified in conjunction with the relevant tools, such as crimping machines.

Product features

For cross-section: 1 mm²

AWG: 18

Length: 8 mm

Internal diameter: 3 mm

Design: for wire processing machines

Colour: Red

Colour code: DIN colour code: yes

For: Crimping machine RC
Crimping machine R8
Crimping machine R8 E

Delivery form: Taped

Packs of: 5000 pc(s).

Weight/pack: 0,13 kg

Copper weight (kg per piece): 0

EAN: 4028177805163

Customs tariff number: 85369010

ETIM 7.0: EC000005

ETIM 6.0: EC000005

eCl@ss 8.0/8.1: 36659290

eCl@ss 6.0/6.1: 36659290

Product description: Wire end ferrules According to DIN colour code

Approvals

Approvals: UR
