

# Rittal – The System.

Faster – better – everywhere.

## **Wire end ferrules loose – AS 4050.760**

Date : 23.9.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Wire end ferrules loose – AS 4050.760

created: 23.09.2020 build on [www.rittal.com/si-sl](http://www.rittal.com/si-sl)



## Product description

**Description:** With plastic collar.

**Technical specifications:** Heat-resistant to 105 °C

**Standards:** AEH DIN 46228

**Material:** E-Cu, galvanic tin-plated  
Plastic collar: Polypropylene

**Note:** UL-certified in conjunction with the relevant tools, such as crimping machines.

## Product features

**For cross-section:** 0,5 mm<sup>2</sup>

**AWG:** 20

**Length:** 8 mm

**Internal diameter:** 2,6 mm

**Design:** for manual wire processing and crimping machines 0.5 - 2.5 mm<sup>2</sup> (length 8 mm)

**Colour:** Orange

**Colour code:** Rittal colour code: yes

<b>For:</b>	Crimping machine L8 manual wire processing
<b>Delivery form:</b>	Loose
<b>Packs of:</b>	500 pc(s).
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177815780
<b>Customs tariff number:</b>	85369010
<b>ETIM 7.0:</b>	EC000005
<b>ETIM 6.0:</b>	EC000005
<b>eCl@ss 8.0/8.1:</b>	36659290
<b>eCl@ss 6.0/6.1:</b>	36659290
<b>Product description:</b>	Wire end ferrules for crimping machines and manual preassembly, 0.5 mm <sup>2</sup> , AWG 20, 8 mm, orange, loosely packed, 500 pc(s).
<b>Approvals</b>	
<b>Approvals:</b>	UR