

# Rittal – The System.

Faster – better – everywhere.

## **Wire end ferrules on a reel – AS 4051.536**

Date : 14.5.2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Wire end ferrules on a reel – AS 4051.536

created: 14.05.2021 build on [www.rittal.com/si-sl](http://www.rittal.com/si-sl)



## Product description

<b>Description:</b>	With plastic collar.
<b>Technical specifications:</b>	Heat-resistant to 105 °C
<b>Material:</b>	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
<b>Note:</b>	UL-certified in conjunction with the relevant tools, such as crimping machines.

## Product description

<b>For cross-section:</b>	0,5 mm <sup>2</sup>
<b>AWG:</b>	20
<b>Length:</b>	10 mm
<b>Internal diameter:</b>	2,9 mm
<b>Design:</b>	for crimping machines, multiple colour codes supported
<b>Colour:</b>	Orange
<b>Colour code:</b>	Rittal colour code: yes Multiple colour codes supported: yes
<b>For:</b>	Crimping machine RC

<b>Delivery form:</b>	Taped
<b>Packs of:</b>	4000 pc(s).
<b>Weight/pack:</b>	4 kg
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177937840
<b>Customs tariff number:</b>	85369010
<b>ETIM 7.0:</b>	EC000005
<b>ETIM 6.0:</b>	EC000005
<b>eCl@ss 8.0/8.1:</b>	36659290
<b>eCl@ss 6.0/6.1:</b>	36659290
<b>Product description:</b>	Wire end ferrules 0.5 mm <sup>2</sup> x 10 mm AWG 20 multinorm, packs of 4,000 pc(s)., colour: orange, delivery form: on belt (in accordance with the Rittal colour code), 0.5 mm <sup>2</sup>

## Approvals

<b>Approvals:</b>	UL + C-UL
-------------------	-----------