

# Rittal – The System.

Faster – better – everywhere.

## Wire end ferrules on a reel – AS 4051.537

Date : 28.1.2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Wire end ferrules on a reel – AS 4051.537

created: 28.01.2021 build on [www.rittal.com/si-sl](http://www.rittal.com/si-sl)



## ECAT (long)

**Description:** With plastic collar.

**Technical specifications:** Heat-resistant to 105 °C

**Material:** E-Cu, galvanic tin-plated  
Plastic collar: Polypropylene

**Note:** UL-certified in conjunction with the relevant tools, such as crimping machines.

## Product features

**For cross-section:** 0,75 mm<sup>2</sup>

**AWG:** 18

**Length:** 10 mm

**Internal diameter:** 3,4 mm

**Design:** for wire processing machines

**Colour:** White

**Colour code:** Rittal colour code: yes  
Multiple colour codes supported: yes

**For:** Crimping machine RC

<b>Delivery form:</b>	Taped
<b>Packs of:</b>	4000 pc(s).
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177937857
<b>Customs tariff number:</b>	85369010
<b>ETIM 7.0:</b>	EC000005
<b>ETIM 6.0:</b>	EC000005
<b>eCl@ss 8.0/8.1:</b>	36659290
<b>eCl@ss 6.0/6.1:</b>	36659290
<b>ECAT (long):</b>	Wire end ferrules 0.75 mm <sup>2</sup> x 10 mm AWG 18 multinorm, packs of 4,000 pc(s)., colour: white, delivery form: on belt (in accordance with the Rittal colour code), 0.75 mm <sup>2</sup>
<b>Approvals</b>	
<b>Approvals:</b>	UL + C-UL