

Rittal – The System.

Faster – better – everywhere.

Wire end ferrules on a reel – AS 4051.597

Date : 11.12.2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wire end ferrules on a reel – AS 4051.597

created: 11.12.2019 build on www.rittal.com/si-sl



Product description

Description:	With plastic collar.
Technical specifications:	Heat-resistant to 105 °C
Material:	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Note:	UL-certified in conjunction with the relevant tools, such as crimping machines.

Product features

For cross-section:	0,5 mm ²
AWG:	20
Length:	8 mm
Internal diameter:	2,6 mm
Design:	for wire processing machines
Colour:	Orange
For:	Crimping machine RC Crimping machine R8 Crimping machine R8 E
Delivery form:	Taped

Packs of:	5000 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177920057
Customs tariff number:	85369010
ETIM 7.0:	EC000005
ETIM 6.0:	EC000005
eCl@ss 8.0/8.1:	36659290
eCl@ss 6.0/6.1:	36659290
Approvals	
Approvals:	UR