

Rittal – The System.

Faster – better – everywhere.

Wire end ferrules on a reel – AS 4051.604

Date : 16.5.2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wire end ferrules on a reel – AS 4051.604

created: 16.05.2021 build on www.rittal.com/si-sl



Product description

Description: With plastic collar.

Technical specifications: Heat-resistant to 105 °C

Material: E-Cu, galvanic tin-plated
Plastic collar: Polypropylene

Note: UL-certified in conjunction with the relevant tools, such as crimping machines.

Product description

For cross-section: 1,5 mm²

AWG: 16

Length: 10 mm

Internal diameter: 3,5 mm

Design: for wire processing machines

Colour: Red

Colour code: Rittal colour code: yes

For: Crimping machine RC

Delivery form:	Taped
Packs of:	5000 pc(s).
Weight/pack:	5 kg
Copper weight (kg per piece):	0
EAN:	4028177938656
Customs tariff number:	85369010
ETIM 7.0:	EC000005
ETIM 6.0:	EC000005
eCl@ss 8.0/8.1:	36659290
eCl@ss 6.0/6.1:	36659290
Product description:	Wire end ferrules 1.5 mm ² x 10 mm AWG 16, packs of 5,000 pc(s)., colour: red, delivery form: on belt (in accordance with the Rittal colour code)
Approvals	
Approvals:	UL + C-UL