

Rittal – The System.

Faster – better – everywhere.

Wire end ferrules on a reel – AS 4051.696

Date : 3.8.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wire end ferrules on a reel – AS 4051.696

created: 03.08.2020 build on www.rittal.com/si-sl



Product description

Description:	With plastic collar.
Technical specifications:	Heat-resistant to 105 °C
Standards:	AEH DIN 46228
Material:	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Note:	UL-certified in conjunction with the relevant tools, such as crimping machines.

Product features

For cross-section:	0,75 mm ²
AWG:	18
Length:	10 mm
Internal diameter:	2,8 mm
Design:	for wire processing machines
Colour:	Grey
Colour code:	DIN colour code: yes

For:	Crimping machine RC
Delivery form:	Taped
Packs of:	5000 pc(s).
Copper weight (kg per piece):	0
EAN:	4028177938625
Customs tariff number:	85369010
ETIM 7.0:	EC000005
ETIM 6.0:	EC000005
eCl@ss 8.0/8.1:	36659290
eCl@ss 6.0/6.1:	36659290
Product description:	Wire end ferrules 0.75 mm ² x 10 mm AWG 18, packs of 5,000 pc(s)., colour: grey, delivery form: on belt (in accordance with the DIN colour code)
Approvals	
Approvals:	UR