

Rittal – The System.

Faster – better – everywhere.

► Network/server enclosure TS IT with glazed door, IP 55, empty enclosure – DK 5504.790

Date : 17.4.2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Network/server enclosure TS IT with glazed door, IP 55, empty enclosure – DK 5504.790

created: 17.04.2021 build on www.rittal.com/si-sl



Discontinued article.

This item will be discontinued on: 20.01.2021

Product description

Material:	Sheet steel Aluminium
Surface finish:	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder-coated
Colour:	Enclosure frame and panels: RAL 7035
Protection category IP to IEC 60 529:	IP 55 only in conjunction with baying seal or screw-fastened side panels
Supply includes:	TS 8 enclosure frame with doors and roof plate Glazed aluminium door at the front (180°) Sheet steel door at the rear, 180° hinges Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E Roof plate, one-piece, solid Base tray with gland plate, multi-piece, solid Baying seal and sealing kit for gland plates (supplied loose) Connection accessories for potential equalisation with earthing point (supplied loose) 12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose) 50 multi-tooth screws, conductive (supplied loose) IPPC pallet

Note: Depending on how and where it is sited, the door opening angle may vary for selected applications
For enclosures with height and depth 2000 x 1200 mm / 2200 x 1000 mm / 2200 x 1200 mm, the matching side panels are optionally available and are supplied fitted to the enclosure

Basic material:	Aluminium
Product description	
Dimensions:	Width: 800 mm Height: 1200 mm Depth: 1000 mm
482.6 mm (19") version:	Without 482.6 mm (19") interior installation
Construction doors:	Sealed, IP 55
Free mounting space to the 482.6 mm (19") level, front/rear:	
Packs of:	1 pc(s).
Weight/pack:	86,2 kg
EAN:	4028177702875
Customs tariff number:	94032080
ETIM 7.0:	EC002499
ETIM 6.0:	EC002499
eCl@ss 8.0/8.1:	27180207
eCl@ss 6.0/6.1:	27180207
Product description:	TS IT, without 482.6 mm (19") interior installation, glazed door, WHD: 800 x 1200 x 1000 mm, 24 U, IP 55
Approvals	
Approvals:	UL + C-UL
Certificates:	NA Protection category
Declarations:	Declaration of conformity