

Rittal – The System.

Faster – better – everywhere.

► **Network/server enclosure TS IT with vented door, with 482.6 mm (19") mounting angles – DK 5528.110**

Date : 16.4.2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Network/server enclosure TS IT with vented door, with 482.6 mm (19") mounting angles – DK 5528.110

created: 16.04.2021 build on www.rittal.com/si-sl



Discontinued article.

This item will be discontinued on: 20.01.2021

Product description

Material:	Sheet steel Aluminium
Surface finish:	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder-coated
Colour:	Enclosure frame and panels: RAL 7035 Interior installation, vent grille at the front: RAL 9005
Supply includes:	TS 8 enclosure frame with doors and roof plate Aluminium/sheet steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E Two 482.6 mm (19") mounting sections front and rear, variably mounted on support strips with quick-release fasteners Spacers, height 50 mm, to raise the cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose) Connection accessories for potential equalisation with earthing point (supplied loose) 12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose) 50 multi-tooth screws, conductive (supplied loose) IPPC pallet Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate Sheet steel rear door, vented (vented surface area approx. 85% perforated), vertically divided, 180° hinges
Note:	Depending on how and where it is sited, the door opening angle may vary for selected applications

Basic material:	Sheet steel
Product description	
Dimensions:	Width: 600 mm Height: 1800 mm Depth: 800 mm
Installation height for components:	38 U
Distance between levels as delivered:	545 mm
482.6 mm (19") version:	Mounting angles, 482.6 mm (19")
Free mounting space to the 482.6 mm (19") level, front/rear:	84 mm / 168 mm
Load capacity:	15000 N
Packs of:	1 pc(s).
Weight/pack:	78 kg
EAN:	4028177703643
Customs tariff number:	94032080
ETIM 7.0:	EC002499
ETIM 6.0:	EC002499
eCl@ss 8.0/8.1:	27180207
eCl@ss 6.0/6.1:	27180207
Product description:	TS IT, 19" mounting angles, vented, WHD: 600 x 1800 x 800 mm, 38 U
Approvals	
Approvals:	UL + C-UL
Certificates:	NA
Declarations:	Declaration of conformity