

Rittal – The System.

Faster – better – everywhere.

Power Distribution Module PDM – DK 7857.320

Date : 19.9.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Power Distribution Module PDM – DK 7857.320

created: 19.09.2020 build on www.rittal.com/si-sl



Discontinued article.

This item will be discontinued on: 30.04.2020

Product description

Design:	4 outlets per 10 kW
Description:	Mechanically latchable and scalable in the PDR.
Supply includes:	482.6 mm (19") module, 3 U Master switch 4 fused 3-phase outlets to the rack 3 x 230 V/16 A per outlet Connected load 400 V/3~, max. 63 A
Options:	RC circuit-breaker

Product features

Dimensions:	Width: 482,6 mm Width: 19" Depth: 350 mm
Packs of:	1 pc(s).
Weight/pack:	8,75 kg
Copper weight (kg per piece):	0
EAN:	4028177450745

Customs tariff number:	85369095
ETIM 7.0:	EC002288
ETIM 6.0:	EC002288
eCl@ss 8.0/8.1:	27142415
eCl@ss 6.0/6.1:	27142604
Product description:	DK Power Distribution Module PDM, WHD: 482,6 (19")x3 Ux350 mm, Output: 4, 3-phase, 230 V, 16 A
Approvals	
Certificates:	EAC
Declarations:	Declaration of conformity