

# Rittal – The System.

Faster – better – everywhere.

## ► Monitor/keyboard unit with 17" TFT display and VGA/DVI connection – DK 9055.410

Date : 21.4.2021

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Monitor/keyboard unit with 17" TFT display and VGA/DVI connection – DK 9055.410

created: 21.04.2021 build on [www.rittal.com/si-sl](http://www.rittal.com/si-sl)



## Product description

**Description:** The unit is housed in a pull-out drawer. The monitor can be flipped up and the drawer latches into the end position. This means that the unit only requires 1 U in the 482.6 mm (19") rack.

**Benefits:** Analog and digital video input  
Cables are safely routed in the energy chain  
Lockable at the front  
Simple, one-man installation.

**Colour:** RAL 9005

**Supply includes:** Monitor/keyboard unit, 1 U  
VGA cable  
DVI cable  
USB cable  
Earthing-pin mains cable  
with 17" TFT display and VGA/DVI connection  
2 PS/2 cables  
Keyboard  
with integral touchpad

**Note on Model No.:** Extended delivery times.

## Product description

**Dimensions:** Width: 482,6 mm  
Width: 19"  
Depth: 680 mm

**Rated operating voltage:** 100 V - 240 V, 1~, 50 Hz/60 Hz

<b>Units:</b>	1 U
<b>Installation dimensions:</b>	Installation depth (min.): 680 mm Installation depth (max.): 850 mm
<b>Operating temperature:</b>	Operation (environment): +5 °C...+45 °C
<b>Power consumption:</b>	Max. power consumption in operation: 32 W Max. power consumption with closed monitor unit: 1 W
<b>Equipment (electrical):</b>	Connector (type): IEC 320 connector C14
<b>Keyboard layout:</b>	German
<b>Display features:</b>	Diagonal: 432 mm (17") Format: 4 : 3 Resolution of display: 1280 x 1024 pixels Number of colours: 16700000 Brightness (typ.): 350 cd/m <sup>2</sup> Contrast ratio: Contrast ratio approx. 1000:1
<b>Interfaces/connections:</b>	General: VGA (D-Sub HD 15-pole) General: DVI General: 1 x USB General: PS/2
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	18,8 kg
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177638396
<b>Customs tariff number:</b>	85286200
<b>ETIM 7.0:</b>	EC001428
<b>ETIM 6.0:</b>	EC001428
<b>eCl@ss 8.0/8.1:</b>	19200201
<b>eCl@ss 6.0/6.1:</b>	27189253
<b>Product description:</b>	DK Monitor/keyboard unit, WHD: 482.6 mm (19")x1 Ux680 mm, 100-240 V, 1~, 50/60 Hz, german, RAL 9005

## Approvals

**Certificates:** EAC

---

**Declarations:** Declaration of conformity

---