

Rittal – The System.

Faster – better – everywhere.

► Connection plate for laminated copper bars – SV 9640.350

Date : 25.1.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Connection plate for laminated copper bars – SV 9640.350

created: 25.01.2020 build on www.rittal.com/si-sl



Product description

Description: For the connection of laminated flat copper bars.

Material: Connection plate: E-Cu
Thrust piece: Stainless steel

Supply includes: Assembly parts

Product features

To fit busbars: Type: Maxi-PLS 45 S/45

To fit laminated copper bars: Qty.: 2
with no. of membranes: 10
with membrane width: 100 mm
with membrane thickness: 1 mm

Clamping area for laminated copper bars: Width: 100 mm
Height: 20 mm

Packs of: 3 pc(s).

Weight/pack: 1,96 kg

Copper weight (kg per piece): 0,27

EAN: 4028177238695

| | |
|-------------------------------|--|
| Customs tariff number: | 85369010 |
| ETIM 7.0: | EC002498 |
| ETIM 6.0: | EC002498 |
| eCl@ss 8.0/8.1: | 27379201 |
| eCl@ss 6.0/6.1: | 27400613 |
| Product description: | SV Connection plate, clamping area WH: 100x20 mm, (Maxi-PLS 1600/2000) |
| Approvals | |
| Approvals: | UR |
| Certificates: | EAC |
| Declarations: | Declaration of conformity |