

Rittal – The System.

Faster – better – everywhere.

CS wall-mounted enclosures – CS 9791.045

Date : 3.8.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS wall-mounted enclosures – CS 9791.045

created: 03.08.2020 build on www.rittal.com/si-sl



Product description

Description:	Outdoor enclosures for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out in the bottom and integrated louvres on the rear panel and side panels for ventilation.
Material:	Enclosure: Aluminium AlMg3 Door: Stainless steel 1.4301 (AISI 304), 1.5 mm Mounting plate: Aluminium, 2 mm
Surface finish:	Enclosure: Powder-coated, UV-resistant pure polyester Mounting plate: Clear chromated
Colour:	RAL 7035
Protection category IP to IEC 60 529:	IP 55
Supply includes:	Double-walled outdoor enclosure, fully preconfigured Inner enclosure with mounting plate, gland plate and security lock Mounting bracket for enclosure internal thermostat or hygrostat Outer enclosure with designer cover and security lock 3524 E 2 C rails on the rear panel 2 security locks
Note:	Extended delivery times.
Basic material:	Aluminium

Product features

Dimensions:	Width: 630 mm Height: 780 mm Depth: 380 mm
--------------------	--

Clearances:	Clearance width: 560 mm Clearance height: 560 mm Clearance depth: 308 mm
Mounting plate:	Width: 550 mm Height: 550 mm
Inner enclosure:	Width: 580 mm Height: 580 mm Depth: 333 mm
Lock version:	Cam
Number of locks:	2
Packs of:	1 pc(s).
Weight/pack:	21 kg
EAN:	4028177193727
Customs tariff number:	94032080
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Product description:	CS Wall-mounted enclosure, WHD: 630x780x380 mm, aluminum, with mounting plate, Enclosure-within-an-enclosure concept
Approvals	
Declarations:	Declaration of conformity