

Rittal – The System.

Faster – better – everywhere.

FlatBox – DK 7507.000

Date : 29.10.2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FlatBox – DK 7507.000

created: 29.10.2020 build on www.rittal.com/sk-sk



Product description

Design:	with 482.6 mm (19") mounting angles
Description:	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits:	Tool-free quick assembly System assembly on the open 482.6 mm (19") frame
Material:	oceľový plech
Surface finish:	Powder-coated
Colour:	RAL 7035
Supply includes:	Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door hinge point selectable Connection components for tool-free, fast assembly Earthing kit for system-compatible earthing of all enclosure parts Profilové lišty 19"
Note:	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 482.6 mm (19") levels: Depth - 104 mm
Basic material:	oceľový plech

Product features

Dimensions: Width: 600 mm
Height: 358 mm
Depth: 400 mm

Installation height for components: 6 U

Load capacity: max. 300 N

Packs of: 1 pc(s).

Weight/pack: 17,84 kg

EAN: 4028177551398

Customs tariff number: 94032080

ETIM 7.0: EC002500

ETIM 6.0: EC002500

eCl@ss 8.0/8.1: 27180208

eCl@ss 6.0/6.1: 27180208

Product description: DK FlatBox, WHD: 600x358x400 mm, 6 U, with 482.6 mm (19") mounting angles

Approvals

Certificates: EAC
