

Rittal – The System.

Faster – better – everywhere.

Hygienic Design HD system enclosure – HD 4000.885

Date : Jul 13, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Hygienic Design HD system enclosure – HD 4000.885

created: 13.07.2020 build on www.rittal.com/uae-en



Product description

Material:	Enclosure and door: Stainless steel 1.4301 (AISI 304) Lock insert HD: Stainless steel 1.4404 (AISI 316L) Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Mounting plate: Sheet steel
Surface finish:	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated Seal: Blue, dyed (RAL 5010)
Protection category IP to IEC 60 529:	IP 66
Protection category IP to DIN 40 050-9:	IP 59K
Supply includes:	Enclosure frame with welded rear panel gland plate Door with inserted seal R/h door hinge with single-door enclosures, may be swapped to opposite side Mounting plate
Options:	HD supporting structure with levelling
Note:	To achieve a protection category of IP 66/IP 59K, the HD versions of the side panel, roof and (where applicable) baying frame must be selected.

Product features

Dimensions:	Width: 800 mm Height: 1800 mm Depth: 500 mm
Material thickness:	Enclosure: 1.5 mm Door: 2 mm

Mounting plate: 3 mm

Mounting plate:	Width: 699 mm Height: 1696 mm
Number of doors:	1
Door opening angle:	125°
Packs of:	1 pc(s).
Weight/pack:	108 kg
EAN:	4028177693593
Customs tariff number:	94032080
ETIM 7.0:	EC000261
ETIM 6.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 6.0/6.1:	27180101
Approvals	
Approvals:	UL + C-UL
Certificates:	Protection category