

# Rittal – The System.

Faster – better – everywhere.

► **Network/server enclosure TS IT with glazed door, pre-configured, with 482.6 mm (19") mounting frame – DK 5503.151**

Date : Nov 24, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Network/server enclosure TS IT with glazed door, pre-configured, with 482.6 mm (19") mounting frame – DK 5503.151

created: 24.11.2020 build on [www.rittal.com/uae-en](http://www.rittal.com/uae-en)



Discontinued article.

Product expires on: 30.04.2021 |||This item is being replaced by: 5303154

## Product description

<b>Material:</b>	Sheet steel Aluminium Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic Glazed door: Single-pane safety glass, 3 mm
<b>Surface finish:</b>	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors, roof and side panels: Dipcoat-primed and powder-coated
<b>Colour:</b>	Enclosure frame and panels: RAL 7035 Interior installation, base/plinth: RAL 9005
<b>Supply includes:</b>	Enclosure frame TS 8 with doors, roof plate, base/plinth and side panels Glazed aluminium door at the front, 180° hinges Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E Two 482.6 mm (19") mounting frames, front and rear, depth-variable Spacers, height 50 mm, to raise the cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose) Connection accessories for potential equalisation incl. central earthing point, pre-configured 12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose) 50 multi-tooth screws, conductive (supplied loose) Base mount Base module mounted at front as infill panel Base/plinth system VX, 100 mm, vented Base/plinth corner pieces and trim panels, sides, screw-fastened Base/plinth trim panels, front and rear plus corner and baying covers supplied loose

Side panels, one-piece, lockable  
 4 levelling feet, M12, including base/plinth adaptor (supplied loose)  
 4 cable clamp rails (T-head) for outer mounting level, to fit enclosure depth (supplied loose)  
 10 cable shunting rings, metal, 125 x 65 mm (supplied loose)  
 IPPC pallet  
 Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate  
 Sheet steel door at the rear, 180° hinges

<b>Note:</b>	Depending on how and where it is sited, the door opening angle may vary for selected applications
<b>Basic material:</b>	Sheet steel
<b>Product features</b>	
<b>Dimensions:</b>	Width: 800 mm Height: 1200 mm Height (enclosure with plinth): 1300 mm Depth: 800 mm
<b>Installation height for components:</b>	24 U
<b>Distance between levels as delivered:</b>	545 mm
<b>482.6 mm (19") version:</b>	Mounting frame, 482.6 mm (19")
<b>Free mounting space to the 482.6 mm (19") level, front/rear:</b>	147 mm / 105 mm
<b>Load capacity:</b>	15000 N
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	118.8 kg
<b>EAN:</b>	4028177705852
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC002499
<b>ETIM 6.0:</b>	EC002499
<b>eCl@ss 8.0/8.1:</b>	27180207
<b>eCl@ss 6.0/6.1:</b>	27180207

**Product description:** TS IT, 19" mounting frame, glazed door, WHD: 800 x 1200 x 800 mm, 24 U, pre-

configured

## Approvals

**Approvals:** UL + C-UL

**Certificates:** EAC

**Declarations:** Declaration of conformity