

Rittal – The System.

Faster – better – everywhere.

► **Network/server enclosure TS IT with glazed door, pre-configured, with 482.6 mm (19") mounting frame – DK 5513.151**

Date : Aug 14, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Network/server enclosure TS IT with glazed door, pre-configured, with 482.6 mm (19") mounting frame – DK 5513.151

created: 14.08.2020 build on www.rittal.com/uae-en



Discontinued article.

Product description

Material:	Sheet steel Aluminium Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic Glazed door: Single-pane safety glass, 3 mm
Surface finish:	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors, roof and side panels: Dipcoat-primed and powder-coated
Colour:	Enclosure frame and panels: RAL 7035 Interior installation, base/plinth: RAL 9005
Supply includes:	Enclosure frame TS 8 with doors, roof plate, base/plinth and side panels Glazed aluminium door at the front, 180° hinges Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E Two 482.6 mm (19") mounting frames, front and rear, depth-variable Spacers, height 50 mm, to raise the cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose) Connection accessories for potential equalisation incl. central earthing point, pre-configured 12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose) 50 multi-tooth screws, conductive (supplied loose) Base mount Base module mounted at front as infill panel Base/plinth system VX, 100 mm, vented Base/plinth corner pieces and trim panels, sides, screw-fastened Base/plinth trim panels, front and rear plus corner and baying covers supplied loose Side panels, one-piece, lockable 4 levelling feet, M12, including base/plinth adaptor (supplied loose)

4 cable clamp rails (T-head) for outer mounting level, to fit enclosure depth (supplied loose)
 10 cable shunting rings, metal, 125 x 65 mm (supplied loose)
 IPPC pallet
 Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate
 Sheet steel rear door, solid, vertically divided, 180° hinges

Note: Depending on how and where it is sited, the door opening angle may vary for selected applications

Basic material: Sheet steel

Product features

Dimensions: Width: 600 mm
 Height: 2200 mm
 Height (enclosure with plinth): 2300 mm
 Depth: 1000 mm

Installation height for components: 47 U

Distance between levels as delivered: 745 mm

482.6 mm (19") version: Mounting frame, 482.6 mm (19")

Free mounting space to the 482.6 mm (19") level, front/rear: 84 mm / 168 mm

Load capacity: 15000 N

Packs of: 1 pc(s).

EAN: 4028177706231

Customs tariff number: 94032080

ETIM 7.0: EC002499

ETIM 6.0: EC002499

eCl@ss 8.0/8.1: 27180207

eCl@ss 6.0/6.1: 27180207

Product description: TS IT, 19" mounting frame, glazed door, WHD: 600 x 2200 x 1000 mm, 47 U, pre-configured

Approvals

Approvals: UL + C-UL

Declarations: Declaration of conformity
