

Rittal – The System.

Faster – better – everywhere.

► **Network/server enclosure TS IT with glazed door, pre-configured, with 482.6 mm (19") mounting frame – DK 5529.151**

Date : Aug 14, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Network/server enclosure TS IT with glazed door, pre-configured, with 482.6 mm (19") mounting frame – DK 5529.151

created: 14.08.2020 build on www.rittal.com/uae-en



Discontinued article.

Product description

Material:	Sheet steel Aluminium Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic Glazed door: Single-pane safety glass, 3 mm
Surface finish:	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors, roof and side panels: Dipcoat-primed and powder-coated
Colour:	Enclosure frame and panels: RAL 7035 Interior installation, base/plinth: RAL 9005
Supply includes:	Enclosure frame TS 8 with doors, roof plate, base/plinth and side panels Glazed aluminium door at the front, 180° hinges Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E Two 482.6 mm (19") mounting frames, front and rear, depth-variable Spacers, height 50 mm, to raise the cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose) Connection accessories for potential equalisation incl. central earthing point, pre-configured 12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose) 50 multi-tooth screws, conductive (supplied loose) Base mount Base module mounted at front as infill panel Base/plinth system VX, 100 mm, vented Base/plinth corner pieces and trim panels, sides, screw-fastened Base/plinth trim panels, front and rear plus corner and baying covers supplied loose Side panels, one-piece, lockable 4 levelling feet, M12, including base/plinth adaptor (supplied loose)

4 cable clamp rails (T-head) for outer mounting level, to fit enclosure depth (supplied loose)
 10 cable shunting rings, metal, 125 x 65 mm (supplied loose)
 IPPC pallet
 Roof plate, multi-piece, removable, for horizontal cable entry at the rear and with covered cut-out for fan mounting plate
 Sheet steel rear door, solid, vertically divided, 180° hinges

Note:	Depending on how and where it is sited, the door opening angle may vary for selected applications
Basic material:	Sheet steel
Product features	
Dimensions:	Width: 600 mm Height: 2000 mm Height (enclosure with plinth): 2100 mm Depth: 600 mm
Installation height for components:	42 U
Distance between levels as delivered:	345 mm
482.6 mm (19") version:	Mounting frame, 482.6 mm (19")
Free mounting space to the 482.6 mm (19") level, front/rear:	84 mm / 168 mm
Load capacity:	15000 N
Packs of:	1 pc(s).
Weight/pack:	126.5 kg
EAN:	4028177706491
Customs tariff number:	94032080
ETIM 7.0:	EC002499
ETIM 6.0:	EC002499
eCl@ss 8.0/8.1:	27180207
eCl@ss 6.0/6.1:	27180207
Product description:	TS IT, 19" mounting frame, glazed door, WHD: 600 x 2000 x 600 mm, 42 U, pre-configured

Approvals

Approvals: UL + C-UL

Declarations: Declaration of conformity
