

Rittal – The System.

Faster – better – everywhere.

► Gland plate for metric cable glands for EL – EL 7705.235

Date : Oct 2, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Gland plate for metric cable glands for EL – EL

7705.235

created: 02.10.2020 build on www.rittal.com/uae-en



Product description

Description: Folded gland plate with foamed-in seal and pre-punched, knock-out holes for metric cable glands M12, M20, M25, M32, M40.

Material: Sheet steel, 1.5 mm

Colour: RAL 7035

**Protection category
IP to IEC 60 529:** IP 55

Product features

To fit: Enclosure type: EL

Dimensions: Width: 599 mm
Depth: 133.5 mm

Cable entry: Number x metric diameter: 4 x M12
Number x metric diameter: 7 x M20
Number x metric diameter: 5 x M25
Number x metric diameter: 2 x M32
Number x metric diameter: 2 x M40

Packs of: 1 pc(s).

Weight/pack: 1.64 kg

**Copper weight (kg
per piece):** 0

EAN:	4028177389854
Customs tariff number:	73269098
ETIM 7.0:	EC000211
ETIM 6.0:	EC000211
eCl@ss 8.0/8.1:	27142421
eCl@ss 6.0/6.1:	27189190
Product description:	EL Gland plate for metric cable glands, WxD: 599x133,5 mm, For EL