

Rittal – The System.

Faster – better – everywhere.

► Base/plinth, stationary for PC, IW – PC 8800.920

Date : Sep 20, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Base/plinth, stationary for PC, IW – PC 8800.920

created: 20.09.2020 build on www.rittal.com/uae-en



Product description

Description: Design-coordinated with the enclosures, with front projection.

Material: Sheet steel, 2.0 mm

Colour: RAL 7035
Design component, front: RAL 7015

Supply includes: 1 design component, front
1 base/plinth component, rear
2 base/plinth trim panels, side

Product features

To fit: Enclosure type: PC
Enclosure type: IW
Width: = 600 mm
Depth: = 600 mm

Dimensions: Height: 100 mm

Packs of: 1 pc(s).

Weight/pack: 13 kg

Copper weight (kg per piece): 0

EAN: 4028177266926

Customs tariff 94039010

number:

ETIM 7.0: EC000721

ETIM 6.0: EC000721

eCl@ss 8.0/8.1: 27182003

eCl@ss 6.0/6.1: 27189270

Product description: PC Base/plinth, stationary, for PC, IW, for D: 600 mm, H: 100 mm, Sheet steel

Approvals

Certificates: EAC
