





Hersteller Manufacturer	Baureihe Series	Typ Model	Bemessungsstrom Rated current	Drehscheibenposition Disk Position		Artikel Nr. Order No.	
				Line	Load	Easy Fix	Universal
ABB	Tmax XT	XT1	160	4	1	9360500	9360600
ABB	Tmax XT	XT2	160	5	3	9360500	9360600
ABB	Tmax XT	XT3	250	1	4	9360512	9360612
ABB	Tmax XT	XT4	250	6	4	9360512	9360612
ABB	Sace Formular	A3	400	3	3	9360525	9360625
ABB	Tmax	T5 400	400	3	3	9360525	9360625
ABB	Tmax XT	XT5 400	400	3	3	9360525	9360625
ABB	Sace Formular	A3	630	3	3	9360535	9360635
ABB	Tmax	T5 630	630	3	3	9360535	9360635
ABB	Tmax XT	XT5 630	630	3	3	9360535	9360635
Chint	NM8	NM8-400 Frame 3	400	1	1	9360525	9360625
Chint	NM8S	NM8S-400 Frame 3	400	1	1	9360525	9360625
Chint	NM8	NM8S-630 Frame 3	630	1	1	9360535	9360635
Chint	NM8S	NM8-630 Frame 3	630	1	1	9360535	9360635
Eaton	LZM	LZM3 400	400	8	8	9360525	9360625
Eaton	NZM	NZM3 400	400	8	8	9360525	9360625
Eaton	LZM	LZM3 630	630	8	8	9360535	9360635
Eaton	NZM	NZM3 630	630	8	8	9360535	9360635
Fuji Electric	BW	BW400 -3P	400	6	6	9360525	9360625
Hager	h3+	P630	630	3	3	9360535	9360635
Hyundai Electric	HGP	400	400	5	5	9360525	9360625
Hyundai Electric	HGP	630AF	630	5	5	9360535	9360635
LS Electric	Metasol	400AF	400	6	6	9360525	9360625
LS Electric	Susol	TS400	400	5	5	9360525	9360625
LS Electric	Susol	TS630	630	5	5	9360535	9360635
Mitsubishi	NF	NF160-SGV	160	2	2	9360512	9360612
Mitsubishi	NF	NF250-SV	250	2	2	9360512	9360612
Mitsubishi	NF	NF400-CW/SW	400	6	6	9360525	9360625
Mitsubishi	NF	NF630-CW/SW	630	6	6	9360535	9360635
OEZ	BH	BH630	630	7	7	9360535	9360635
Rockwell	140G Frame Size G	140G-G6C3-D10	100	4	1	9360500	9360600
Rockwell	140G Frame Size H	140G-H6F3-D10	100	5	3	9360500	9360600
Rockwell	140G Frame Size G	140G-G2C3-D12	125	4	1	9360500	9360600
Rockwell	140G Frame Size H	140G-H6F3-D12	125	5	3	9360500	9360600
Rockwell	140G Frame Size G	140G-G6E3-D16	160	4	1	9360500	9360600
Rockwell	140G Frame Size H	140G-H6F3-D16	160	5	3	9360500	9360600
Rockwell	140G Frame Size I	140G-I2C3	225	1	4	9360512	9360612
Rockwell	140G Frame Size J	140G-J6F3-D25	250	6	4	9360512	9360612
Rockwell	140G	Frame Size K	400	3	3	9360525	9360625
Rockwell	140G2	Frame Size K	400	3	3	9360525	9360625
Rockwell	140G	Frame Size L	630	3	3	9360535	9360635
Rockwell	140G2	Frame Size L	630	3	3	9360535	9360635

Hersteller Manufacturer	Baureihe Series	Typ Model	Bemessungsstrom Rated current	Line	Load	Easy Fix	
						Universal	
Schneider Electric	ComPacT NSX100	NSX100	100	5	3	9360512	9360612
Schneider Electric	EasyPact EZC	100 A	100	3	4	9360500	9360600
Schneider Electric	ComPacT NSXm	NSXm160	160	2	2	9360500	9360600
Schneider Electric	ComPacT NSX160	NSX160	160	5	3	9360512	9360612
Schneider Electric	TeSys GV5	GV5	220	5	1	9360512	9360612
Schneider Electric	EasyPact EZC	EZC250H	250	3	2	9360512	9360612
Schneider Electric	ComPacT NSX250	NSX250	250	5	3	9360512	9360612
Schneider Electric	ComPacT	NSX400	400	2	2	9360525	9360625
Schneider Electric	EasyPact	CVS	400	2	2	9360525	9360625
Schneider Electric	EasyPact	EZC	400	2	2	9360525	9360625
Schneider Electric	ComPacT	NSX630	630	2	2	9360535	9360635
Schneider Electric	EasyPact	CVS	630	2	2	9360535	9360635
Schneider Electric	EasyPact	EZC	630	2	2	9360535	9360635
Schrack	MC	MC3	400	8	8	9360525	9360625
Schrack	MC	MC3	630	8	8	9360535	9360635
Siemens	3VA1	3VA10	100	7	6	9360500	9360600
Siemens	3VA2	3VA20	100	6	4	9360512	9360612
Siemens	3VA5	3VA51	125	1	1	9360500	9360600
Siemens	3VA1	3VA11	160	7	6	9360500	9360600
Siemens	3VA2	3VA21	160	6	4	9360512	9360612
Siemens	3VA2	3VA22	250	6	4	9360512	9360612
Siemens	3VA1	3VA13	400	1	1	9360525	9360625
Siemens	3VA2	3VA23	400	1	1	9360525	9360625
Siemens	3VA5	3VA53	400	1	1	9360525	9360625
Siemens	3VA6	3VA63	400	1	1	9360525	9360625
Siemens	3VA1	3VA14	630	1	1	9360535	9360635
Siemens	3VA2	3VA24	630	1	1	9360535	9360635
Siemens	3VA5	3VA54	630	1	1	9360535	9360635
Siemens	3VA6	3VA64	630	1	1	9360535	9360635
Terasaki	Tembreak2	S400	400	3	3	9360525	9360625
Terasaki	Tembreak2	E630, S630	630	3	3	9360535	9360635