


# Rittal – The System.

Faster – better – everywhere.



## AX 2584.100 Pole clamp

State: 27/04/2024 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2584.100 - Pole clamp for AX, KX, AX plastic, AX IT, CS wall-mounted enclosures

For reliable, convenient fastening to round or square poles.



## Features

Model No.	AX 2584.100
Product description	For reliable, convenient fastening to round or square poles.
Technical specifications	For pole diameter: Ø from 40 to 170 mm For pole size: □ from 50 to 150 mm
Material	Mounting angles, clamping section: Sheet steel Clamping strap: Stainless steel 1.4301 (AISI 304)
Surface finish	Mounting angle, clamping section: Zinc-plated
Supply includes	2 mounting angles, 600 mm long 4 clamping sections 2 clamping straps 4 clamping brackets 4 self-tapping M10 bolts for mounting onto the enclosure
Note	Only suitable for enclosures up to a width of 600 mm. Pole clamping cannot be used in conjunction with a protective roof for AX.
To fit	Enclosure type: AX KX AX plastic AX IT CS wall-mounted enclosures AX outdoor housing

# Features

Type rating to UL 50E	Type 1, 3R, 4, 12
Packs of	2 pc(s).
Weight/pack	1.92 kg
Customs tariff number	83024900
EAN	4028177940598
E-Number Sweden	E3465274
ETIM 7.0	EC002625
ECLASS 8.0	27189234

# Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------