


Rittal – The System.

Faster – better – everywhere.



VX 8001.224 Gland plate

State: 10/3/2026 (Source: www.rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8001.224 - Gland plate for VX, VX IT, VX SE

For individual configuration of the floor space. Potential equalization is achieved via assembly components and earthing points.

Features

Model No.	VX 8001.224
Product description	For individual configuration of the floor space. Potential equalization is achieved via assembly components and earthing points.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Note	At least one sliding plate is required to fully seal a base opening. For two-door enclosures, one pack is sufficient for one half of the enclosure
Dimensions	Width: 440 mm Depth: 275 mm Width: 17.3 " Depth: 10.8 "
Suitable for	Enclosure type: VX VX IT VX SE CX One-Piece Console CX Pedestal Width: = 1,000 mm Enclosure type: VX VX IT VX SE CX One-Piece Console CX Pedestal Width: = 39.4 "
Packaging unit	1 pc(s).
Net weight	1.6 kg

Features

Gross weight	1.7 kg
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	VX Gland plate, WD: 1000x275 mm

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------