

Rittal – The System.


Faster – better – everywhere.

SE 8 / TS 8 Floor Stand and SE 8 Solid Base Pan Kits



The SE8/ TS8 floor stand and SE8 solid base pan kits augment Rittal's standard offering of SE8/ TS8 industrial enclosures and provide users with enhanced flexibility to meet the challenges of their applications. The floor stand kits are 12" high and available in RAL 7035 (light gray) powder-coated, 11-gauge carbon steel and 304 or 316L brushed stainless steel and in depths of 16, 20 and 24 inches.

The kits are intended to elevate SE8/ TS8 enclosures in applications where separation between the floor and the enclosure are necessary due to environmental hazards or cable conduit installation/access concerns.



Used in conjunction with the aforementioned floor stands, Rittal's SE8 solid base pan kits serve as an alternative to the standard SE8 cable gland plate base configuration and provide a solid, heavy-duty surface at the bottom of the SE8 enclosure. The base pans are available in RAL 7035 (light gray) powder-coated 14-gauge carbon and 304 brushed stainless

steel and come in a variety of widths and depths to cover the entire SE8 product family. They are internally fastened to the enclosure and include a foamed-in-place gasket seal to ensure the SE8 type 12, 3R or 4/4X environmental protection.

- Maintains existing SE8 enclosure UL Type rating (12, 3R, 4/4X*)
- Easily installed on the bottom of SE8 enclosures
- All assembly hardware is included
- Can be used in conjunction with 12" leg kits with UL Type rating maintained

*Note: SE8/TS8 Type 4/ 4X single door enclosures come with solid base pan already installed from the factory

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



Floor Stand Kits

PART NUMBER	DESCRIPTION
9963522	SE8/ TS8 Floor Stand Kits - 305x400mm
9963523	SE8/ TS8 Floor Stand Kits - 305x500mm
9963524	SE8/ TS8 Floor Stand Kits - 305x600mm
9963525	SE8/ TS8 Floor Stand Kits - 305x400mm - 304SS
9963526	SE8/ TS8 Floor Stand Kits - 305x500mm - 304SS
9963527	SE8/ TS8 Floor Stand Kits - 305x600mm - 304SS
9963528	SE8/TS8 Floor Stand Kits - 305x400mm-316L SS
9963529	SE8/TS8 Floor Stand Kits - 305x500mm-316L SS
9963530	SE8/TS8 Floor Stand Kits - 305x600mm-316L SS

Solid Base Pan

PART NUMBER	DESCRIPTION
9957900	SE8 SOLID BASE PAN 0600W0400D
9957901	SE8 SOLID BASE PAN 0800W0400D
9957902	SE8 SOLID BASE PAN 0800W0500D
9957903	SE8 SOLID BASE PAN 0800W0600D
9957904	SE8 SOLID BASE PAN 1000W0400D
9957905	SE8 SOLID BASE PAN 1200W0400D
9957906	SE8 SOLID BASE PAN 1200W0500D
9957907	SE8 SOLID BASE PAN 1200W0600D
9957908	SE8 SOLID BASE PAN 1600W0400D
9957909	SE8 SOLID BASE PAN 1800W0500D
9957910	SE8 SOLID BASE PAN S-S 304 0600W0400D
9957911	SE8 SOLID BASE PAN S-S 304 0600W0500D
9957912	SE8 SOLID BASE PAN S-S 304 0800W0500D
9957913	SE8 SOLID BASE PAN S-S 304 0800W0600D
9957914	SE8 SOLID BASE PAN S-S 304 1000W0400D
9957915	SE8 SOLID BASE PAN S-S 304 1200W0500D



Rittal's SE8 solid base pan kits serve as an alternative to the standard SE8 cable gland plate base configuration and provide a solid, heavy-duty surface at the bottom of the SE8 enclosure.

Rittal North America LLC

Woodfield Corporate Center • 425 North Martingale Road, Suite 400 • Schaumburg, Illinois 60173 • USA
 Phone: 937-399-0500 • Toll-free: 800-477-4000 • Email: rittal@rittal.us • Website: www.rittal.com



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES