

# Rittal – The System.

Faster – better – everywhere.

## Compact enclosures AE – AE 1030.500

Date : Jun 6, 2023

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Compact enclosures AE – AE 1030.500

created: 06.06.2023 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Discontinued article.

This item will be discontinued on: 30.09.2020 |||This item is being replaced by: 1576000

### Product description

<b>Material:</b>	Enclosure: Sheet steel Door: Sheet steel, all-round foamed-in PU seal
<b>Surface finish:</b>	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 66
<b>Protection category NEMA:</b>	NEMA 4
<b>IK Code:</b>	IK08
<b>Supply includes:</b>	Enclosure with hinged door(s), of all-round solid construction Gland plate(s) in enclosure base Mounting plate Lock: 3 mm double-bit
<b>Basic material:</b>	Sheet steel

### Product description

<b>Dimensions:</b>	Width: 380 mm Height: 300 mm Depth: 155 mm
--------------------	--

<b>Material thickness:</b>	Enclosure: 1.38 mm Door: 1.5 mm Mounting plate: 2 mm
<b>Mounting plate:</b>	Width: 334 mm Height: 275 mm
<b>Number of doors:</b>	1
<b>Door hinged on the right, may be swapped to the left:</b>	yes
<b>Lock version:</b>	Cam
<b>Number of locks:</b>	1
<b>Lock insert:</b>	3 mm double-bit
<b>Gland plate, size:</b>	3
<b>Gland plate, qty.:</b>	1
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	7.4 kg
<b>EAN:</b>	4028177251960
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC000261
<b>ETIM 6.0:</b>	EC000261
<b>eCl@ss 8.0/8.1:</b>	27180101
<b>eCl@ss 6.0/6.1:</b>	27180101
<b>Product description:</b>	AE Compact enclosure, WHD: 380x300x155 mm, Sheet steel, with mounting plate, single-door, with one cam lock

## Approvals

<b>Approvals:</b>	Bureau Veritas DNV-GL Lloyds Register of Shipping RRR UL + C-UL
-------------------	---

---

<b>Certificates:</b>	Certificate of manufacturer according to RMRS IK-Code NA Protection category
----------------------	---

---

<b>Declarations:</b>	Declaration of conformity
----------------------	---------------------------

---