

# Rittal – The System.

Faster – better – everywhere.

## **Baying systems TS 8 – TS 8226.500**

Date : Sep 19, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Baying systems TS 8 – TS 8226.500

created: 19.09.2020 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Discontinued article.

This item will be discontinued on: 15.02.2019 |||This item is being replaced by: 8226000

## Product description

<b>Material:</b>	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel, 3.0 mm
<b>Surface finish:</b>	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 55
<b>Protection category NEMA:</b>	NEMA 12
<b>IK Code:</b>	IK09
<b>Supply includes:</b>	Enclosure frame Door(s) R/h door hinge with single-door enclosures, may be swapped to opposite side Roof plate Rear panel 4 eyebolts Lock: 3 mm double-bit Gland plates Mounting plate 2 TS punched rails 18 x 38 mm 2 support strips fitted in the enclosure depth

<b>Product modification:</b>	TS 8 and the SE 8 both come with the new mounting plate of the baying enclosure system VX25.
<b>Basic material:</b>	Sheet steel
<b>Product features</b>	
<b>Dimensions:</b>	Width: 1200 mm Height: 2200 mm Depth: 600 mm
<b>Mounting plate:</b>	Width: 1099 mm Height: 2096 mm
<b>Number of doors:</b>	2
<b>2 support strips fitted in the enclosure depth:</b>	yes
<b>Packs of:</b>	1 pc(s).
<b>Weight/pack:</b>	208 kg
<b>EAN:</b>	4028177250901
<b>Customs tariff number:</b>	94032080
<b>ETIM 7.0:</b>	EC000261
<b>ETIM 6.0:</b>	EC000261
<b>eCl@ss 8.0/8.1:</b>	27180101
<b>eCl@ss 6.0/6.1:</b>	27180101
<b>Product description:</b>	TS Bayed enclosure system, WHD: 1200x2200x600 mm, Sheet steel, with mounting plate, two doors at the front
<b>Approvals</b>	
<b>Approvals:</b>	Bureau Veritas CSA DNV-GL Lloyds Register of Shipping RRR Russian Maritime Register of Shipping TÜV UL + C-UL

**Certificates:** Certificate of manufacturer according to RMRS  
EAC  
IK-Code  
Protection category  
Protection category IP 55 (CPRI)

---

**Declarations:** Declaration of conformity  
Manufacturer's declaration

---