

# Rittal – The System.

Faster – better – everywhere.

## ► Profil za uvođenje kabela, srednji za TS, CM, TP – TS 8802.120

Date : 2020.08.03

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Profil za uvođenje kabela, srednji za TS, CM, TP – TS 8802.120

created: 03.08.2020 build on [www.rittal.com/hr-hr](http://www.rittal.com/hr-hr)



Discontinued article.

## Product description

|  |  |
|--|--|
| <b>Description:</b>                          | For sealing the cable entry between the gland plates.  |
| <b>Benefits:</b>                             | Particularly well-suited to cables with identical cross-sections   |
| <b>Applications:</b>                         | For top-mounting on gland plates.  |
| <b>Material:</b>                             | Extruded aluminium section<br>Foam rubber cable clamp strip: PU foam   |
| <b>Technical specifications:</b>             | Foam rubber cable clamp strip: Cross-section: 30 x 25 mm   |
| <b>Protection category IP to IEC 60 529:</b> | IP 55 if installed correctly   |
| <b>Supply includes:</b>                      | Plug-in sections, incl. foam rubber clamp strip  |
| <b>Note:</b>                                 | 2 pc(s). are sufficient for one base opening up to an enclosure width of 800 mm<br>From an enclosure width of 1000 mm, two base openings are provided. 4 packs per enclosure may be fitted |

## Product features

|                |  |
|----------------|--|
| <b>To fit:</b> | Enclosure type: TS<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Width: = 1200 mm |
|----------------|--|

|                                      |  |
|--------------------------------------|--|
| <b>Packs of:</b>                     | 4 pc(s).   |
| <b>Weight/pack:</b>                  | 0,43 kg  |
| <b>Copper weight (kg per piece):</b> | 0  |
| <b>EAN:</b>                          | 4028177382510  |
| <b>Customs tariff number:</b>        | 76042990   |
| <b>ETIM 7.0:</b>                     | EC000211   |
| <b>ETIM 6.0:</b>                     | EC000211   |
| <b>eCl@ss 8.0/8.1:</b>               | 27142421   |
| <b>eCl@ss 6.0/6.1:</b>               | 27400604   |
| <b>Product description:</b>          | TS Section for cable entry, centre, for TS, SE, CM, TP, for W: 1200 mm |
| <b>Approvals</b>                     |  |
| <b>Certificates:</b>                 | EAC  |