

# Rittal – The System.

Faster – better – everywhere.

## Adapter za uređaje CB 3-polni – SV 9635.110

Date : 2021.04.19

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Adapter za uređaje CB 3-polni – SV 9635.110

created: 19.04.2021 build on [www.rittal.com/hr-hr](http://www.rittal.com/hr-hr)



## Product description

|                            |  |
|----------------------------|--|
| <b>Function principle:</b> | For mechanical attachment and direct contacting of circuit-breakers on the board<br>Circuit-breaker is fitted using variably adjustable fixing points (M4)   |
| <b>Material:</b>           | Polyamide<br>Fire protection corresponding to UL 94-V0   |
| <b>Colour:</b>             | RAL 7035   |
| <b>Note:</b>               | Consider the mounting distance of the circuit-breaker when selecting the circuit-breaker component adaptor<br>Depending on the circuit-breaker used, there may be a reduction in output<br>The technical data may vary for UL applications |

## Product description

|                                 |  |
|---------------------------------|--|
| <b>Number of poles:</b>         | 3-pole   |
| <b>Dimensions:</b>              | Width: 90 mm<br>Height: 160 mm<br>Depth: 45 mm |
| <b>Rated current max.:</b>      | 160 A  |
| <b>Rated operating voltage:</b> | 690 V (AC), 3~<br>600 V (DC), 3~               |
| <b>Cable outlet:</b>            | Top/bottom                                     |
| <b>Mounting distance:</b>       | 30 mm  |

|                                      |  |
|--------------------------------------|--|
| <b>To fit manufacturer (model):</b>  | ABB (XT2)<br>Allen Bradley (140G-H)<br>Eaton (NZM1)<br>Schneider Electric (NSXm)                       |
| <b>Packs of:</b>                     | 1 pc(s).   |
| <b>Weight/pack:</b>                  | 0,59 kg  |
| <b>Copper weight (kg per piece):</b> | 0  |
| <b>EAN:</b>                          | 4028177951846  |
| <b>Customs tariff number:</b>        | 85369095   |
| <b>ETIM 7.0:</b>                     | EC001531   |
| <b>ETIM 6.0:</b>                     | EC001531   |
| <b>eCl@ss 8.0/8.1:</b>               | 27370304   |
| <b>eCl@ss 6.0/6.1:</b>               | 27370304   |
| <b>Product description:</b>          | SV CB component adaptor 160 A, 690 V (AC), 600 V (DC), 3-pole WH: 90 x 160 mm, mounting distance 30 mm |
| <b>Approvals</b>                     |  |
| <b>Approvals:</b>                    | UL + C-UL  |