



Hersteller Manufacturer	Baureihe Series	Typ Model	Bemessungsstrom Rated current	Artikel Nr. Order No.		Drehscheibenposition Disk Position	
				Easy Fix	Universal	Line	Load
ABB	Tmax XT	XT1	160 A	9360500	9360600	4	1
ABB	Tmax XT	XT2	160 A	9360500	9360600	5	3
ABB	Tmax XT	XT3	250 A	9360512	9360612	1	4
ABB	Tmax XT	XT4	250 A	9360512	9360612	6	4
ABB	Sace Isomax	S5 400	400 A	9360525	9360535	1	1
ABB	Tmax	T5 400	400 A	9360625	9360635	3	3
ABB	Tmax XT	XT5 400	400 A	9360525	9360535	3	3
ABB	Sace Isomax	S5 630	630 A	9360625	9360635	1	1
ABB	Tmax	T5 630	630 A	9360525	9360535	3	3
ABB	Tmax XT	XT5 630	630 A	9360625	9360635	3	3
Chint	NM8N	NM8N-400	400 A	9360525	9360535	1	1
Chint	NXM	NXM-400S	400 A	9360625	9360635	6	6
Chint	NXMS	NXMS-400	400 A	9360525	9360535	6	6
Chint	NM8N	NM8N-630	630 A	9360625	9360635	1	1
Chint	NXM	NXM-630S	630 A	9360525	9360535	6	6
Chint	NXMS	NXMS-630	630 A	9360625	9360635	6	6
Eaton	NZM	NZM3 400	400 A	9360525	9360535	8	8
Eaton	NZM	NZM3 630	630 A	9360625	9360635	8	8
Fuji Electric	BW	BW400_-3P	400 A	9360525	9360535	6	6
Hager	X630	X630	630 A	9360625	9360635	3	3
Hyundai Electric	HGM	400AF	400 A	9360525	9360535	6	6
Hyundai Electric	HGP	400	400 A	9360625	9360635	5	5
Hyundai Electric	HGP	630AF	630 A	9360525	9360535	5	5

Hersteller Manufacturer	Baureihe Series	Typ Model	Bemessungsstrom Rated current	Easy Fix	Universal	Line	Load
LS Electric	Metasol	400AF	400 A	9360525 9360625	9360535 9360635	6	6
LS Electric	Susol	TS400	400 A	9360525 9360625	9360535 9360635	5	5
LS Electric	Susol	TS630	630 A	9360525 9360625	9360535 9360635	5	5
Mitsubishi	NF	NF160-SGV	160 A	9360512	9360612	2	2
Mitsubishi	NF	NF250-	250 A	9360512	9360612	2	2
Mitsubishi	NF	NF400-SW	400 A	9360525 9360625	9360535 9360635	6	6
Mitsubishi	NF	NF630-SW	630 A	9360525 9360625	9360535 9360635	6	6
OEZ	BH	BH630	630 A	9360525 9360625	9360535 9360635	7	7
Rockwell	140G Frame Size G	100 A	100 A	9360500	9360600	4	1
Rockwell	140G Frame Size H	100 A	100 A	9360500	9360600	5	3
Rockwell	140G Frame Size G	125 A	125 A	9360500	9360600	4	1
Rockwell	140G Frame Size H	125 A	125 A	9360500	9360600	5	3
Rockwell	140G Frame Size G	160 A	160 A	9360500	9360600	4	1
Rockwell	140G Frame Size H	160 A	160 A	9360500	9360600	5	3
Rockwell	140G Frame Size I	225 A	225 A	9360512	9360612	1	4
Rockwell	140G Frame Size J	250 A	250 A	9360512	9360612	6	4
Rockwell	140G	140G-K0F3-D40	400 A	9360525 9360625	9360535 9360635	3	3
Rockwell	140G	140G-M0F3-D63	630 A	9360525 9360625	9360535 9360635	3	3
Schneider Electric	EasyPact EZC	100 A	100 A	9360500	9360600	3	4
Schneider Electric	ComPacT NSX100	100 A	100 A	9360512	9360612	5	3
Schneider Electric	ComPacT NSXm	160 A	160 A	9360500	9360600	2	2
Schneider Electric	ComPacT NSX160	160 A	160 A	9360512	9360612	5	3
Schneider Electric	TeSys GV5	220 A	220 A	9360512	9360612	5	1
Schneider Electric	EasyPact EZC	250 A	250 A	9360512	9360612	3	2
Schneider Electric	ComPacT NSX250	250 A	250 A	9360512	9360612	5	3
Schneider Electric	ComPact NSX400	NSX400	400 A	9360525 9360625	9360535 9360635	2	2
Schneider Electric	ComPact NSX630	NSX630	630 A	9360525 9360625	9360535 9360635	2	2
Schrack Brand Eaton	NZM3	MC3 630	630 A	9360525 9360625	9360535 9360635	8	8
Siemens	3VA1	3VA10	100 A	9360500	9360600	7	6
Siemens	3VA2	3VA20	100 A	9360512	9360612	6	4
Siemens	3VA5	3VA51	125 A	9360500	9360600	1	1
Siemens	3VA1	3VA11	160 A	9360500	9360600	7	6
Siemens	3VA2	3VA21	160 A	9360512	9360612	6	4

Hersteller Manufacturer	Baureihe Series	Typ Model	Bemessungsstrom Rated current	Easy Fix	Universal	Line	Load
Siemens	3VA2	3VA22	250 A	9360512	9360612	6	4
Siemens	3VA2	3VA23	400 A	9360525 9360625	9360535 9360635	1	1
Siemens	3VA2	3VA24	630 A	9360525 9360625	9360535 9360635	1	1
Terasaki	Tembreak2	S400	400 A	9360525 9360625	9360535 9360635	3	3
Terasaki	Tembreak2	E630/S630	630 A	9360525 9360625	9360535 9360635	3	3